


**RoHS
Compliant**




Features

- End stackable
- Gold contact for high reliability


Electrical Specifications

Contact Arrangement	: SPST
No. of Poles	: 2, 3, 4, 5, 6, 7, 8, 9, 10, 12 Pole
Contact Rating	: 25mA, 24VDC
Contact Resistance	: 100mΩ Max.
Insulation Resistance	: 100MΩ Min. 500V DC
Dielectric Strength	: 500V AC/1 minute
Operating Force	: 1,000gf max.
Travel	: 1mm
Operating Life	: 2,000 cycles
Operating Temperature	: -20°C to +85°C
Storage Temperature	: -40°C to +85°C

CIRCUIT



Diagram



Dimensions : Millimetres

Part Number Table

Description	"A" mm	"B" mm	Part Number
DIP Switch, Top Tape Sealed, Slide Type, 2Pole, SPST, Recessed Actuator, Black/White, SMD	4.98	2.54	MCEMR-02-T
DIP Switch, Top Tape Sealed, Slide Type, 3Pole, SPST, Recessed Actuator, Black/White, SMD	7.52	5.08	MCEMR-03-T
DIP Switch, Top Tape Sealed, Slide Type, 4Pole, SPST, Recessed Actuator, Black/White, SMD	10.06	7.62	MCEMR-04-T
DIP Switch, Top Tape Sealed, Slide Type, 5Pole, SPST, Recessed Actuator, Black/White, SMD	12.6	10.16	MCEMR-05-T
DIP Switch, Top Tape Sealed, Slide Type, 6Pole, SPST, Recessed Actuator, Black/White, SMD	15.14	12.7	MCEMR-06-T
DIP Switch, Top Tape Sealed, Slide Type, 7Pole, SPST, Recessed Actuator, Black/White, SMD	17.68	15.24	MCEMR-07-T
DIP Switch, Top Tape Sealed, Slide Type, 8Pole, SPST, Recessed Actuator, Black/White, SMD	20.22	17.78	MCEMR-08-T
DIP Switch, Top Tape Sealed, Slide Type, 9Pole, SPST, Recessed Actuator, Black/White, SMD	22.76	20.32	MCEMR-09-T
DIP Switch, Top Tape Sealed, Slide Type, 10Pole, SPST, Recessed Actuator, Black/White, SMD	25.3	22.86	MCEMR-10-T
DIP Switch, Top Tape Sealed, Slide Type, 12Pole, SPST, Recessed Actuator, Black/White, SMD	30.38	27.94	MCEMR-12-T

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.