

NEMA 4 Enclosures

SNB Series NEMA Sheet Metal Boxes



Designed to meet NEMA 1, 2, 4, 4x, 12, 13 and IP66 ratings. UL listed and tested to UL508-4X, UL meets UL50E requirements

NEW!! Additional large size boxes, with enhanced design and continuous gasket (^) for superior performance.

Design Features

- Continuous seam welded 16 ga. steel or [stainless steel](#) construction
- Hinged cover clamps to the base with keyed quarter turn latch for a watertight seal
- External mounting brackets allow box to be mounted on a wall or panel without having to remove the cover and exposing internal components to the environment
- Bonding studs for grounding are provided on base and door
- Internal panel and hardware included
- UL Listed Type 1, 2, 4, 4X and 12. IP65 and IP66 ratings
- Easily machined and modified to your particular requirements
- Finish: Smooth Gray powder coat, Internal Panel - Clear Zinc plate

New Design features

- Rigid door design
- Continuous gasket
- Bar folded flange to enhance seal performance
- Additional rubber washer inside mounting brackets to enhance water resistant seal
- Added locks in larger size enclosures

SNB SERIES NEMA 4 SHEET METAL BOX WITH MOUNTING BRACKETS										
Catalog Number	Drawings	External Dimensions (Base)			Wall Mounting Dimensions		Internal Panel Dimensions		Wgt. Lbs.	304 Stainless Steel Version
Powder Coated Steel		Height	Width	Depth	Height	Width	Height	Width		Catalog Number
SNB-3730	PDFDXF	9.84"	7.87"	5.91"	11.14"	6.42"	8.46"	5.91"	7	SNB-3730-SS
SNB-3731	PDFDXF	11.81"	9.84"	5.91"	13.11"	8.39"	10.43"	7.87"	9	SNB-3731-SS
SNB-3732	PDFDXF	11.81"	9.84"	7.87"	13.06"	8.39"	10.43"	7.87"	11	SNB-3732-SS
SNB-3733	PDFDXF	11.81"	11.81"	5.91"	13.11"	10.35"	10.43"	9.84"	11	SNB-3733-SS
SNB-3734	PDFDXF	11.81"	11.81"	7.87"	13.11"	10.35"	10.43"	9.84"	12	SNB-3734-SS
SNB-3735	PDFDXF	15.75"	11.81"	5.91"	17.05"	14.29"	14.37"	9.84"	15	SNB-3735-SS
SNB-3736	PDFDXF	15.75"	11.81"	7.87"	17.05"	14.29"	14.37"	9.84"	16	SNB-3736-SS
SNB-3737	PDFDXF	15.75"	15.75"	7.87"	17.05"	14.29"	14.37"	13.78"	22	SNB-3737-SS
SNB-3738	PDFDXF	7.87"	5.91"	5.91"	9.17"	4.46"	6.49"	3.94"	5.2	SNB-3738-SS
SNB-3739	PDFDXF	7.87"	7.87"	3.98"	9.17"	6.42"	6.49"	5.91"	4.6	SNB-3739-SS
SNB-3740	PDFDXF	9.84"	9.84"	5.91"	11.14"	8.39"	8.46"	7.87"	9.7	SNB-3740-SS
SNB-3741	PDFDXF	9.84"	7.87"	3.98"	11.14"	6.42"	8.46"	5.91"	5.7	SNB-3741-SS
SNB-3743	PDFDXF	15.75"	13.98"	7.87"	17.05"	12.53"	14.37"	12.01"	19.8	SNB-3743-SS
SNB-3746	PDFDXF	20"	16"	8"	21.27	14.54	18.62	14.03	20.3	SNB-3746-SS
SNB-3749	PDFDXF	20"	20"	12"	21.27	18.54	18.62	18.03	29.4	SNB-3749-SS
SNB-3751	PDFDXF	24"	16"	8"	25.27	14.54	22.62	14.03	23.5	SNB-3751-SS
SNB-3752	PDFDXF	24"	20"	8"	25.27	18.54	22.62	18.03	27.8	SNB-3752-SS
SNB-3754	PDFDXF	24"	24"	10"	25.27	22.54	22.62	22.03	35.3	SNB-3754-SS