




CUSTOMER'S APPROVAL: \_\_\_\_\_ DATE: \_\_\_\_\_

FIRST ARTICLE SAMPLE REQUIRED:  YES,  NO.

PINOUT CONFIGURATION



P/N	L±mm
104911101	1000±50
104911102	2000±50
104911103	3000±100



NOTE:

1. THIS ITEM CONTAINS PAT. US 6,287,148 B1 RF-BLOK™ SHIELDING DESIGN.

2. WIRE MARKING:

VDC LONDON WWW.VDCTRADING.COM

E193793 RJ AWM 20276 80°C 30V VW-1 DVI-I DUAL LINK A+D

UNIT: mm

ITEM	DESCRIPTION	QTY.	UNIT
1	DVI MALE CONNECTOR (24+5)	2	PCS.
2	BLACK MOLDED PVC HOOD W/VDC LOGO	2	PCS.
3	RF-BLOK™	2	PCS.
4	BLACK #4/40 THUMBSREW	4	PCS.
5	UL20276 (28AWG COAX+SPIRAL)x4C+ (30AWGx1PAIR+AL-FOIL+MYLAR+DRAIN)x7C +(28AWG WIRE)x6C+AL-FOIL+MYLAR+BRAID OVERALL; BLACK PVC JACKET	SEE	DWG.