

SXP SOLDERING & REWORK CARTRIDGES		Compatible with: MFR-1110, MFR-1161, MFR-2211, MFR-2241 Systems and MFR-H1-SC hand-piece	
HOOF		<p>SFP-DRH05 STP-DRH05 SCP-DRH05</p>	<p>Hoof, (<math>\varnothing</math> x L) 0.5 x 15.21 mm (.02" x .6")</p>
		<p>SFP-DRH610 STP-DRH610 SCP-DRH610</p>	<p>Hoof, 60°. (<math>\varnothing</math> x L) 1.0 x 11.6 mm (.04" x .45")</p>
		<p>SFP-DRH15 STP-DRH15 SCP-DRH15</p>	<p>Hoof, 30°, (<math>\varnothing</math> x L) 1.5 x 16.5 mm (.06" x .65")</p>
		<p>SFP-DRH615 STP-DRH615 SCP-DRH615</p>	<p>Hoof, 60°. (<math>\varnothing</math> x L) 1.5 x 11.6 mm (.06" x .46")</p>
		<p>SFP-DRH35 STP-DRH35 SCP-DRH35</p>	<p>Hoof, 60°, Long Reach, (<math>\varnothing</math> x L) 3.5 x 17.78 mm (.14" x .7")</p>
KNIFE		<p>SFP-DRK50 STP-DRK50 SCP-DRK50</p>	<p>Knife, (W x L) 5.0 x 16 mm (.20" x .63")</p>
CONCAVE-HOOF		<p>SFP-WV15 STP-WV15 SCP-WV15</p>	<p><b>Concave Hoof,</b> (Bevel/L) 60° x 3 mm, (<math>\varnothing</math> x L) 1.5 x 11.6 mm</p>
		<p>SFP-WV20 STP-WV20 SCP-WV20</p>	<p><b>Concave Hoof,</b> (Bevel/L) 60° x 4 mm, (<math>\varnothing</math> x L) 2.0 x 11.6 mm</p>
		<p>SFP-WV30 STP-WV30 SCP-WV30</p>	<p><b>Concave Hoof,</b> (Bevel/L 60°) x 6 mm, (<math>\varnothing</math> x L) 3.0 x 11.6 mm</p>

F = FR4 / Fiber Glass, for most standard applications T = Temperature Sensitive C = Ceramic for high thermal demand applications