



Sample photo

Order symbol: UL PC 125/125 HG
Product nbr: 6411310
Description: UL Enclosure, PC
Remarks: Grey cover

EAN: 6418074014351
EI. number:
Finland:
Electric No. 8212030200
Denmark:
Electric No. Italy: 7351065U

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	130	125	Ingress Protection (EN 60529): IP66/IP67
inch:		5.1	5.1	4.9	Impact Resistance (EN 62262): IK08
					Electrical insulation: Totally insulated
					Halogen free (DIN/VDE 0472, Part 815): 1
					UV resistance: UL 508
					Flammability Rating: UL 746C 5"
					UL Type:
					Glow Wire Test (IEC 695-2-1) °C: 960
Materials:					Certificates:
Material:		Polycarbonate			Underwriters Laboratories
Base colour:		RAL 7035 -light grey			SGS Fimko
Cover screws material:		Polyamide			UL Canada
Cover colour:		RAL 7035 -light grey			Gost R
Cover screws colour:		Grey			
Gasket material:		TPE			
Temperatures:					
Temperature °C (short term):		-40 ... 120 °C			
Temperature °C (continuous):		-40 ... 80 °C			
Temperature °F (short term):		-40 ... 250 °F			
Temperature °F (continuous):		-40 ... 175 °F			

