

Click | Mechanical Feel Keyboard



Same Satisfaction for a fraction of the price.

The Click Keyboard is the go to choice for first time gamers and people looking for a great experience on a budget. With the click satisfaction you would expect from a mechanical keyboard and durability of a premium keyboard, nothing about this feels like a compromise.



Easily adjust the colour of mode of the click and illuminate every key, colours include Red, Green, Blue, Cyan, White, Purple and Yellow.



Responsive 19 Key Anti-Ghosting

Never worry about duplicate key strokes in game again. With 19 Key anti-ghosting every press will be registered.





Specifications

Connectivity:	USB
Keyboard Qty:	105
Cable Length:	1.8m
LED Colour:	7 (Red, Green, Blue, Cyan, White, Purple & Yellow)
Working Power:	5V=200mA
M.T.B.F:	10 Million Keystrokes
Multimedia Functions :	FN + F1-F12
F1:	Open Default Media Player Program
F2:	Decrease System Volume
F3:	Increase System Volume
F4:	Mute System Volume
F5:	Stop Current Media Track
F6:	Play Previous Media Track
F7:	Play Or Pause Current Media Track
F8:	Play Next Media Track
F9:	Open Default E-mail Program (Not Web-Mail)
F10:	Open Home Page
F11:	Lock Keys
F12:	Open Calculator
Anti Ghosting:	19 Keys
Key Elasticity :	>15g
Pre-Travel Distance of Keys:	1.2+/-0.3mm
Total Travel Distance of Keys:	3.6+/-0.3mm

Working Environment Temperature :	0°C to +55°C
Operating Humidity:	10°C to 40°C
Working Voltage:	+5V \pm 0.25V
Working Current:	200mA (330mA max.)
Software Compatibility :	Windows 2000 / XP / VISTA / 7 / 8 / 10 / Linux
Net Weight:	810g \pm 10g

General Specifications

Manufacturer Part Number:	GMX-CLICK
EAN Number:	5055492407832
Has Mains Plug:	No
Colour:	Black / Silver
What's In The Box:	Keyboard
Manual	
Unit (Product) Dimensions (mm): (W x H x D)	447mm x 38mm x 142mm
Packaging Dimensions (mm): (W x H x D)	472mm x 192mm x 46mm
Net Weight (KGs):	0.94 KGs
Gross Weight (KGs):	1.13 KGs



For more information please contact your sales rep.