


REV.	DATE	DESCRIPTION
NC	04/10/07	INITIAL RELEASE



8				<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.</small> <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:</small> 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm <small>UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:</small> .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	<h1 style="color: blue;">Amphenol Connex</h1>				
7					DRAWN	G.R.S.		04/10/07	PART DESCRIPTION <h2 style="text-align: center;">BNC JACK TO SMB PLUG ADAPTER</h2>		
6					CHECKED					PART NO. <h2 style="text-align: center;">242185</h2>	
5					ISSUED						DWG. NO. 242185.DWG
4	CONTACT PIN	BER. COPPER	GOLD		1	SHEET		1 OF 1			
3	INSULATOR	TEFLON	NATURAL	1							
2	SMB BODY	BRASS	GOLD	1							
1	BNC BODY	BRASS	NICKEL	1							
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE	C:/242/242185.DWG				