GQM1875C2E2R0DB12# "#" indicates a package specification code.
















0.5mm min.

0603 (1608M)

< List of part numbers with package codes > GQM1875C2E2R0DB12D

Shape



References

| Packaging | Specifications | Minimum quantity |
|-----------|---------------------|------------------|
| D | φ180mm Paper taping | 4000 |

| Mass (typ.) | | |
|-------------|-------|--|
| 1 piece | 6.3mg | |
| φ180mm Reel | 144g | |

Specifications

Size code in inch(mm)

Distance between external terminals g

| Capacitance | 2.0pF ±0.5pF |
|--|--------------|
| Rated voltage | 250Vdc |
| Temperature characteristics (complied standard) | C0G(EIA) |
| Temperature coefficient | 0±30ppm/°C |
| Temperature range of temperature characteristics | 25 to 125°C |
| Operating temperature range | -55 to 125℃ |

1 of 1



^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



^{2.} This datasheet has only typical specifications because there is no space for detailed specifications.