


Model Number

NBB7-F104M-A2-200MM-V1

Features

- 7 mm embeddable
- 4-wire DC
- Metal housing

Connection



Pinout



Wire colors in accordance with EN 60947-5-2


1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Accessories

V1-G-2M-PVC Cable socket, M12, 4-pin, PVC cable V1-W-2M-PVC

Cable socket, M12, 4-pin, PVC cable

Dimensions



Technical Data

General specifications
Curitohing alamont fun

Switching element function PNP NO/NC
Rated operating distance s_n 7 mm
Installation embeddable
Output polarity DC

Nominal ratings

Operating voltage U_B 10 ... 30 V DC Switching frequency f 150 Hz Reverse polarity protected reverse polarity protected

Ambient conditions

Ambient temperature -25 ... 70 °C (-13 ... 158 °F)

Mechanical specifications

Connection type Cable connector M12 x 1 , 4-pin with PUR cable 200 mm
Housing material GD-Zn
Sensing face PA 12

IP67

Protection degree

Compliance with standards and directives

Standard conformity

Standards IEC / EN 60947-5-2:2004

Approvals and certificates

UL approval cULus Listed, General Purpose

CCC approval Products with a maximum operating voltage of ≤36 V do not bear a CCC marking because they do not require approval.

www.pepperl-fuchs.com