

STUDIO



SRH550DJ



SRH750DJ



SRH840



SRH940

Designed for DJ mixing and personal listening

Engineered for live professional DJ mixing and monitoring

Optimized for professional studio recording

Designed for critical listening, monitoring and mastering

Closed-Back, Supra-aural

Closed-Back, Circumaural

Closed-Back, Circumaural

Closed-Back, Circumaural

50 mm dynamic, neodymium magnet

50 mm dynamic, neodymium magnet

40 mm dynamic, neodymium magnet

40 mm dynamic, neodymium magnet

109 dB/mW

106 dB/mW

102 dB/mW

100 dB/mW

32 Ω

40 Ω

44 Ω

42 Ω

3000 mW

3000 mW

1000 mW

1000 mW

5 Hz – 22 kHz

5 Hz – 30 kHz

5 Hz – 25 kHz

5 Hz – 30 kHz

.52 lb (235 g)

.64 lb (291 g)

.82 lb (372 g)

.71 lb (322 g)

Straight, attached oxygen-free copper

Coiled, single-exit, detachable oxygen-free copper

Coiled, single-exit, detachable oxygen-free copper

Single-exit, detachable oxygen-free copper

2 m (6.56 ft)

3 m (9.84 ft)

3 m (9.84 ft)

Coiled: 3 m (9.84 ft)  
Straight: 2.5 m (8.2 ft)

Gold-plated 1/8" (3.5mm) stereo jack

Gold-plated 1/8" (3.5mm) stereo jack

Gold-plated 1/8" (3.5mm) stereo jack

Gold-plated 1/8" (3.5mm) stereo jack

