


KEMET Part Number: SBCP-14HY100B
(SBCP14HY100B)

KEMET, SBCP-14HY, Power, 10 uH, 20%, 5mm



Dimensions

D	12mm MAX
L	15mm MAX
S	5mm +/-0.5mm
LL	3.5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Weight:	6 g
Packaging:	Bulk
Packaging Quantity:	1500

General Information

Series:	SBCP-14HY
Style:	Through-Hole
Description:	Radial Leaded, Ferrite Power Inductors
Features:	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS:	Yes
Lead:	Wire Leads
Core:	Ferrite

Specifications

Inductance:	10 uH (0.01 MHz)
Inductance Tolerance:	20%
Temperature Range:	-20/+105C
Shielded:	No
Current:	3 Amps
DC Resistance:	0.04 Ohms