

Han-Eco 16B-HTE-for SL-M32-glanded



Part number	19 43 116 0447
Specification	Han-Eco 16B-HTE-for SL-M32-glanded
HARTING eCatalogue	https://b2b.harting.com/19431160447

Identification

Category	Hoods/Housings	
Series of hoods/housings Han-Eco [®] B		
Type of hood/housing	Hoods	
Description of hood/ housing	With integrated cable gland	

Version

Locking type	Single locking lever
Size	16 B
Version	Top entry
Cable entry	1x M32

Technical characteristics

Limiting temperature	-40 +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66
Clamping range	13 21 mm

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Product data sheet 19 43 116 0447 Han-Eco 16B-HTE-for SL-M32-glanded



Commercial data

Packaging size	1
Net weight	182 g
Country of origin	Germany
European customs tariff number	85389099