

# Han-Eco 24B Outd-HSM1-with SL-M40



Part number	19 43 224 0253
Specification	Han-Eco 24B Outd-HSM1-with SL-M40
HARTING eCatalogue	https://b2b.harting.com/19432240253

### Identification

Category	Hoods/Housings
Series of hoods/housingsHan-Eco® B	
Type of hood/housing	Surface mounted housing

#### Version

Locking type	Single locking lever
Size	24 B
Version	Side entry
Cable entry	1x M40

### Technical characteristics

Limiting temperature	-40 +125 °C
Number of relockings	≥500
Degree of protection acc. to IEC 60529	IP66

## Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Colour (seal)	RAL 7001 (silver-grey)
Material (locking)	Polyamide Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0

# Specifications and approvals

Specifications	IEC 61984
Specifications	EN 45545-2 R22: HL1, HL2, HL3



# Specifications and approvals

EN 45545-2 R23: HL1, HL2, HL3
EN 45545-2 R24: HL1, HL2, HL3

#### Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099