

## Han-Eco 16B Outd-HSM2-w. DL-M40-glanded



|                    |   |
|--------------------|---|
| Part number        | 19 43 316 0273  |
| Specification      | Han-Eco 16B Outd-HSM2-w. DL-M40-glanded   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19433160273">https://b2b.harting.com/19433160273</a> |

### Identification

|                             |                             |
|-----------------------------|-----------------------------|
| Category                    | Hoods/Housings              |
| Series of hoods/housings    | Han-Eco® B                  |
| Type of hood/housing        | Surface mounted housing     |
| Description of hood/housing | With integrated cable gland |

### Version

|              |                      |
|--------------|----------------------|
| Locking type | Double locking lever |
| Size         | 16 B                 |
| Version      | Side entry           |
| Cable entry  | 2x M40               |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Number of relockings                   | ≥500            |
| Degree of protection acc. to IEC 60529 | IP66            |
| Clamping range                         | 16 ... 28 mm    |

### Material properties

|   |                                     |
|---|-------------------------------------|
| Material (hood/housing)                   | Polyamide<br>Fibre-glass reinforced |
| Colour (hood/housing)                     | RAL 9005 (jet black)                |
| Material (seal)                           | FPM                                 |
| Colour (seal)                             | RAL 7001 (silver-grey)              |
| Material (locking)                        | Polyamide<br>Fibre-glass reinforced |
| Colour (locking)                          | RAL 9005 (jet black)                |
| Material flammability class acc. to UL 94 | V-0                                 |



Pushing Performance

## Material properties

Material flammability class acc. to UL 94 (locking levers) V-0

## Specifications and approvals

|                |                               |
|----------------|-------------------------------|
| Specifications | IEC 61984                     |
|                | EN 45545-2 R22: HL1, HL2, HL3 |
|                | EN 45545-2 R23: HL1, HL2, HL3 |
|                | EN 45545-2 R24: HL1, HL2, HL3 |

## Commercial data

|                                |          |
|--------------------------------|----------|
| Packaging size                 | 1        |
| Country of origin              | Germany  |
| European customs tariff number | 85389099 |