



KPS SMD Auto X7R, Ceramic, Commercial Grade, 47 uF, 20%, 25 VDC, X7R, 2220-2

TOP VIEW
 Single or Double Chip Stack



SIDE VIEW
 Double Chip Stack



Dimensions

L	6mm +/-0.5mm
W	5mm +/-0.5mm
T	5mm +/-0.50mm
B	1.6mm +/-0.3mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	200

General Information

Supplier:	KEMET
Series:	KPS SMD Auto X7R
Style:	Stacked Chip
Description:	SMD, MLCC, Stacked, Double Chip, Class II, Automotive Grade
Features:	Automotive Grade
RoHS:	Yes
Termination:	Tin
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours
Chip Size:	2220-2
Shelf Life:	78 Weeks
MSL:	1

Specifications

Capacitance:	47 uF
Capacitance Tolerance:	20%
Voltage DC:	25 VDC
Dielectric Withstanding Voltage:	62.5 V
Temperature Range:	-55/+125C
Temperature Coefficient:	X7R
Dissipation Factor:	3.50% 120Hz 25C
Aging Rate:	3% Loss/Decade Hour
Insulation Resistance:	11 MOhms