


**KEMET Part Number: ALC10C103EC063**  
(A521HE103M063C)

ALC10, Aluminum Electrolytic, 85C, 10,000 uF, 20%, 63 VDC, -40/+85C



General Information	
Supplier:	KEMET
Series:	ALC10
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	4 Pin
Notes:	Dimensions D And L Include Slewing
Shelf Life:	156 Weeks

Dimensions	
D	40mm +1mm
L	35mm +/-2mm
S	22.5mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Weight:	57 g
Slewing:	Yes
Packaging:	Bulk, Bag

Specifications	
Capacitance:	10,000 uF
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.45 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 29000 Hrs (Rated Voltage At 85C)
Resistance:	80 mOhms (100Hz 20C), 72 mOhms (10kHz 20C)
Ripple Current:	4.58 Amps (100Hz 85C), 4.67 Amps (10kHz 85C)
Leakage Current:	3780 uA (5min 20C)