


**KEMET Part Number: 400MS12ACMA1STD**  
(A902GP400V120A)

MS/A902, Aluminum Electrolytic, Motor Start, 400 uF, -0/+25%, 120 VAC, -20/+60C



Dimensions	
D	38mm +/-0.5mm
L	116mm MAX

Packaging Specifications	
Packaging:	Bulk, Bag

General Information	
Supplier:	KEMET
Series:	MS/A902
Dielectric:	Aluminum Electrolytic
Description:	Motor Start Aluminum Electrolytic
RoHS:	Yes
Lead:	Quick Connect
Shelf Life:	156 Weeks

Specifications	
Capacitance:	400 uF
Capacitance Tolerance:	-0/+25%
Voltage AC:	120 VAC
Temperature Range:	-20/+60C
Rated Temperature:	60C
Life:	500 Hrs