


KEMET Part Number: C44AMGP5300ZA0J



C44A, Film, Metallized Polypropylene, Power, 30 uF, 5%, 450 VAC, 850 VDC



Dimensions

D	65mm +/-0.5mm
L	138mm +/-2mm
S	22.3mm +/-0.5mm

Packaging Specifications

Mounting:	Bolt - M12x12.5
Packaging:	Bulk, Bag
Packaging Quantity:	12

General Information

Supplier:	KEMET
Series:	C44A
Dielectric:	Metallized Polypropylene
Style:	Can
RoHS:	Yes
Lead:	Threaded Studs M6
Miscellaneous:	Thermal Resistance = 3.2 C/W

Specifications

Capacitance:	30 uF
Capacitance Tolerance:	5%
Voltage AC:	450 VAC
Voltage DC:	850 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Max dV/dt:	40 V/us
Resistance:	5 mOhms (TYP)
Ripple Current:	32 Amps, 1200 Amps (Peak)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

