


C4AT, Film, Metallized Polypropylene, Power, 1 uF, 5%, 400 VAC, 700 VDC, 70C, Lead Spacing = 27.5mm



Dimensions

L	32mm NOM
H	24.5mm NOM
T	15mm NOM
S	27.5mm +/-0.4mm
S1	5.1mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	192

General Information

Supplier:	KEMET
Series:	C4AT
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Switching
RoHS:	Yes
Lead:	4 Wire Leads

Specifications

Capacitance:	1 uF
Capacitance Tolerance:	5%
Voltage AC:	400 VAC
Voltage DC:	700 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Dissipation Factor:	0.05%
Max dV/dt:	119 V/us
Resistance:	6.3 mOhms (100kHz)
Ripple Current:	13 Amps (100kHz 70C), 119 Amps (Peak)