


C44A, Film, Metallized Polypropylene, Power, 50 uF, 5%, 250 VAC, 400 VDC



Dimensions

D	50mm +/-0.5mm
L	101mm +/-2mm
S	22.3mm +/-0.5mm

Packaging Specifications

Mounting:	Bolt - M8x10
Packaging:	Bulk, Bag
Packaging Quantity:	25

General Information

Supplier:	KEMET
Series:	C44A
Dielectric:	Metallized Polypropylene
Style:	Can
RoHS:	Yes
Lead:	Threaded Studs M6
Miscellaneous:	Thermal Resistance = 2.6 C/W

Specifications

Capacitance:	50 uF
Capacitance Tolerance:	5%
Voltage AC:	250 VAC
Voltage DC:	400 VDC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Max dV/dt:	20 V/us
Resistance:	6 mOhms (TYP)
Ripple Current:	25 Amps, 1000 Amps (Peak)