

# Plugs

## 4 mm system



### 4 mm system

<b>Product description</b>	Multiple-spring wire plug with coupling located parallel to the connector pin. In this way, the plugs can be connected together without shorting. Solder connection up to maximum cable cross-section of 1.5 mm <sup>2</sup> . Nickel-plated brass contact material.	Fully mating connector, shatter-proof, flexible insulated sleeve. The tapering sleeve end also serves as kinking protection for the lead. Screw connection up to maximum cable cross-section of 1.5 mm <sup>2</sup> . Nickel-plated brass contact material.
	<b>BSB 300 schwarz/black</b>	<b>VON 20 rot/red</b>
	931 294-100	930 046-101
	4 mm System	4 mm System
	black	red
	red color, order no. 931 294-101	black color, order no. 930 046-100; blue color, order no. 930 046-102; yellow color, order no. 930 046-103; green color, order no. 930 046-104
<b>Drawing</b>		
<b>Technical data</b>	4 mm pin (spring-loaded), socket solder DC 60 V 16 A 3 mOhm	4 mm pin (spring-loaded) screw DC 60 V 16 A 3 mOhm
<b>Material</b>	brass nickel-plated PP	brass nickel-plated PVC-P
<b>Environmental conditions</b>	-25 °C to +100 °C	-25 °C to +70 °C
<b>Inflammability class</b>	94 V-2	94 V-2