


T356, Tantalum, MnO2 Tantalum, Commercial Grade, 100 uF, 10%, 20 VDC, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 5.08mm



General Information

Supplier:	KEMET
Series:	T356
Dielectric:	MnO2 Tantalum
Style:	Radial
Description:	Radial, Solid Tantalum, Conformal, Dipped
Features:	Low Leakage, Reverse Voltage
RoHS:	Yes
Termination:	Tin
Notes:	Longest Lead Is Positive

Dimensions

D	10.2mm
H	18.6mm
S	5.08mm +/-0.38mm
LL	4.75mm +/-0.81mm
F	0.5mm +/-0.05mm

Specifications

Capacitance:	100 uF
Capacitance Tolerance:	10%
Voltage DC:	20 VDC (85C), 13 VDC (125C), 0.2 VDC (125C Reverse)
Temperature Range:	-55/+125C
Dissipation Factor:	8.00%
Leakage Current:	4.3 uA

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	100