


KEMET Part Number: SC-02-30G
(UALSC0230G0000)



KEMET, SC-G/GS, AC Line Filters, Common Mode, 3000 uH



*Pin pitch values are for reference only. Values are not guaranteed.

Dimensions

L	17.5mm MAX
T	14mm MAX
H	17.5mm MAX
LL	15mm +/-2mm
S	13mm NOM

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	1300
Weight:	9 g

General Information

Series:	SC-G/GS
Style:	Through-Hole
RoHS:	Yes
Notes:	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous:	Temperature Rise Maximum: 40 K

Specifications

Voltage AC:	250 VAC
Inductance:	3 mH
Current:	2 A
Temperature Range:	-25/+105C
DC Resistance:	85 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

