


KEMET, M4, Flex Suppressors, RFID



General Information	
<b>Series:</b>	M4
<b>Style:</b>	Sheet
<b>Description:</b>	Flex Suppressor Halogen Free Type
<b>Features:</b>	High Magnetic Permeability Type, Low Magnetic Loss Type
<b>RoHS:</b>	Yes
<b>Qualifications:</b>	UL94 HB, UL File No. E176124
<b>Environment:</b>	Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions	
<b>Sheet Size</b>	240x240mm
<b>L</b>	240mm NOM
<b>W</b>	240mm NOM
<b>T</b>	0.1mm NOM

Specifications	
<b>Temperature Range:</b>	-40/+105C
<b>Magnetic Permeability:</b>	40 u At 13.56MHz
<b>Effective Frequency:</b>	13.56 MHz Max
<b>Resistance:</b>	10 MOhms MIN
<b>Specific Gravity:</b>	3.1 Atm TYP

Packaging Specifications	
<b>Tape Description:</b>	Without PET Tape (Txx00)
<b>Tape Thickness:</b>	0.03mm
<b>Weight:</b>	19.04 g