


KEMET, SSHB10HS, AC Line Filters, Dual Mode, 0.023 H



Dimensions	
L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	10mm +/-0.5mm

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	300
Weight:	10 g

General Information	
Series:	SSHB10HS
Style:	Through-Hole
RoHS:	Yes
Notes:	Marking: R07 Lot No.
Miscellaneous:	Temperature Rise Maximum: 50 K

Specifications	
Voltage AC:	250 VAC
Inductance:	23 mH (10 kHz)
Current:	700 mA
Temperature Range:	-25/+120C
DC Resistance:	810 mOhms