


KEMET, PL, Proximity, SMD, Pyroelectric Infrared



General Information	
Series:	PL
Type:	Proximity
Style:	SMD
Description:	SMD, Low Profile
Notes:	0.3 - 0.9 mV MAX (Source Voltage. Noise 200 mV MAX)

Specifications	
Temperature Range:	-40/+70C
Voltage DC:	600 mV MIN (Output), 2 - 15 (Supply Voltage)
Miscellaneous:	Field of View +/-60 degrees. Warm Up Time: 30 Sec (MAX)

Dimensions	
L	5mm NOM
W	4.8mm NOM
T	1.7mm NOM

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	2000
Weight:	100 mg