











## Colour Options









Green

## Orthomat® Premium The ultimate in durable anti-fatigue mats

- Dual fused layer construction for superior comfort and durability.

  Tough PVC foam textured top surface for excellent resilience
- against wear and tear.
- Low density under layer provides extremely effective underfoot cushioning.
- Exceptional fatigue-relief properties a real investment for the workplace.
- Ideal for demanding locations, especially where regular turning is involved.
- Tapered edges to reduce trip hazards.
- Range of colours available.

## Technical Specification

Material:	Virgin Closed Cell PVC (Foam)		
Surface Finish:	Pebble		
Product Height:	12.5mm		
Roll Length:	18.3m		
Operating Temperature:	0°C to +60°C		
Environmental Resistance:	Suitable for dry indoor environments		
Typical Applications:	Production lines, assembly areas, packing stations, workbenches and retail cashier stations		
Installation Method:	Loose lay		
Cleaning Method:	Brush/Mop the top surface		
Flame Retardancy:	Conforms to BS EN 13501-1:2002 Class Efl		
Country of Origin:	China		
Guarantee:	3 year guarantee when used in a dry environment		

Sizes	Black	Blue	Green	Weight
0.6m x 0.9m	FF010001	-	-	2.00 kg
0.9m x 1.5m	FF010002	-	-	4.99 kg
0.9m x 18.3m	FF010003	FF020003	FF040003	61.00 kg
0.9m x per linear metre	FF010003C	FF020003C	FF040003C	3.80 kg
0.9m x 3.65m	FF010004	-	-	12.15 kg
0.6m x 18.3m	FF010005	-	-	45.60 kg
0.6m x per linear metre	FF010005C	-	-	2.49 kg
1.2m x 18.3m	FF010006	-	FF040005	93.50 kg
1.2m x per linear metre	FF010006C	-	-	5.10 kg