



Part Number: UK-F2

Description: LED Flashlight

The UK-F2 is a high powered flashlight with a 375 Lumen output from its high power CREE LED. Comprising of 2 x AA batteries, it has multiple lighting modes. This includes two dim settings, and a 8hz flash for emergency use. IP66 the flashlight is tough and suitable for all conditions. Die cast aluminium housing makes the UK-F2 a solid and dynamic portable light, and the torch weighs only 150g. A push pull speed focus enables the user greater control over the spread of light. It can also help illuminate objects up to 175m away.



Speed Focus

The flashlight is a solid flashlight built for the hardest of tasks. IP66 the LED torch is fully weatherproof for all conditions meaning greater performance. Power and brightness combine to ensure only the highest specification for the UK-F2.

Additional information

Brand	<i>Prosafe</i>
Battery	<i>2 x AA</i>
LED	<i>CREE</i>
Lumens	<i>375</i>
Beam Distance	<i>175m</i>
Run Time	<i>2 – 60 hrs</i>
IP Rating	<i>IP66</i>
Weight	<i>150g</i>
Height	<i>158 mm</i>
Width	<i>29 mm</i>