

PS12_LHMS_0000_O209E_M0

Description

12 set pigtail, E2000, MM, fiber 0.9mm_XX.X_fiber colour EN / IEC, OM2



Features	Features
- Automatic metal shutter in connector for dust protection and laser safety	
- One-piece design for easy termination	
- Colour coding of connector	
- Mechanical coding of connector	
- Ideal for HighPower applications	
- Switchable duplex clips	

Technical Data

General Data

Description	Values
General Typ	FLSH pigtail
Operation temperature	up to °C
UL Rating	UL 94 V-0
RoHS compliant 2001/65/EU	Yes
REACH compliant	Yes


Connector left

Description	Values
Connector typ	FLSH pigtail
Polish	UPC
Color Housing	Beige
Color Boot	Black
Design connector acc. To	IEC 61754-15, TIA 604-16
Performance class H+S	0
Return Loss	>35dB
Durability	1000

Cable

Description	Values
Cable typ	Semi-tight Tube
Fiber count	1
Fiber	1 x 0.9 mm
Fiber typ	G50/125-OM2 G.651

Technical Drawing



PS12_LHMS_0000_O209E_M0

Ordering information

Meter (m)	Item number	Description
-----------	-------------	-------------