

Product availability : Stock - Normally stocked in distribution facility



Price* : 66.00 USD



Main

Range of product	9080GCB
Product or component type	Circuit Protector
Trip Unit Type	Thermal-magnetic
Electrical Connection	Box lugs

Complementary

Protection type	Overcurrent
Contact operation	Trip-free
Device application	Industrial application
Line Rated Current	1 A
Number of Poles	1P
System Voltage	250 V AC 65 V DC
Wire Size	AWG 16...AWG 10 (copper)
Wire stripping length	0.5 in
Terminal Tightening Torque	7 lbf.in control circuit cage type connector
Terminal Rating	Factory wiring only
Operating Temperature	-22...140 °F
Calibration Temperature	70 °F
Mounting support	35 mm DIN rail 9080GH track
Height	3.45 in
Width	3.15 in
Depth	0.5 in

Environment

Product certifications	CE UL recognized E233026 CCN QVNU2 CSA file 025490 class 3211 07
Standards	UL 1077 DIN 57470 CSA C22.2 No 235

Ordering and shipping details

Category	21703 - 9080 GCB
Discount Schedule	CP5
GTIN	00785901481089
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14999999999999999
Returnability	Y
Country of origin	DE

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0934 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------