

9080GP6

Terminal Block, Pressure Wire Clamp, Natural
Colored Block, 600VAC/DC 40AMP

Product availability : Stock - Normally stocked in distribution facility



Price* : 2.60 USD



Main

| | |
|---------------------------|-------------------------|
| Range of product | 9080G |
| Product or component type | Terminal block |
| Product | Terminal block standard |
| Color | Natural |
| Quantity | Set of 50 |


Complementary

| | |
|---|--|
| System Voltage | 600 V AC/DC |
| Current Rating | 40 A per: UL 40 A per: CSA |
| Wire Size | AWG 18...AWG 12 (copper) |
| Mounting Type | 35 mm DIN rail 9080GH track |
| Certifications | CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01 |
| Material | Nylon block Tin plated brass busbar |
| Electrical Connection | Pressure wire clamp |
| Ambient air temperature for operation | -40...257 °F |
| Electrical Connection Tightening Torque | Clamp terminal zinc plated steel Tightening Torque: 18...20 lbf.in for: AWG 18...AWG 10 (copper) |
| Height | 1.48 in |
| Width | 1.8 in |
| Depth | 0.37 in |
| Density | 32 per foot |
| Compatible End Barrier | GP6B |

Ordering and shipping details

| | |
|-----------------------|--------------------------|
| Category | 21702 - 9080 G (NOT GCB) |
| Discount Schedule | CP5 |
| GTIN | 00785901155379 |
| Nbr. of units in pkg. | 50 |
| Package weight(Lbs) | 0.02 |
| Returnability | Y |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 0841 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity |
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| - - - - - Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| - - - - - More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|