

Description

The 836-P *No Clean Flux Pen* contains a homogenous mixture of halogen-free, low-solids organic flux. It exhibits excellent wetting and fluxing activities, and it leaves essentially no residue on the assembly after soldering. The 836-P *No Clean Flux Pen* may be used for both leaded and lead-free applications. A chiseled tip provides exact delivery of the flux to the surface.

Application & Usages

The 836-P pen is designed to dispense flux precisely. It is excellent for prototyping and rework/repair of printed circuit boards. It works well on switches, sockets, heat sinks, chip carriers, and surface mounted device pads.

Features and Benefits

- **Halogen-free**
- **Excellent wetting**
- **Bright, shiny solder joints**
- **Low residue**
- **Rosin/Resin free**
- **Compatible with lead-free & leaded solder systems**

Flux Paste Properties

<i>Flux Properties</i>	<i>Method</i>	<i>Value</i>
Flux type		Organic
Flux Activity		Low
Halides %(wt)		<0.05%
Flux Classification	J-STD-004	ORL0
Acid number		28–30
Copper Mirror	IPC-TM-650 2.3.32	Pass (no complete breakthrough)
Corrosion Test	IPC-TM-650 2.6.15	Pass (non-corrosive)
Spot Test—Fluorides		Pass (no color change)
Silver Chromate—Chlorides + Bromides	IPC-TM-650 2.3.33	Pass (no discoloration)
Surface insulation resistance (SIR)		
SIR, J-STD-004	IPC-TM-650 2.6.3.3	>1 × 10 ¹¹ Ω
Bellcore compliant		Yes
Cleaning requirements	—	None
<i>Physical Properties</i>	<i>Method</i>	<i>Value</i>
Color		Colorless
Solids%		3.0%–3.6%
Density		0.80
Flash Point	Closed cup	12 °C [53 °F]

Storage and Shelf Life

Store at around room temperature and protect from direct heat or sunlight.

<i>Properties</i>	<i>Value</i>
Shelf Life after DOM Storage Temperature	2 y 18 to 27 °C [65 to 80 °F]

DOM = date of manufacture

Cleaning

If removal is desired, a solvent system like the *MG 4140* or *MG 413B* can be used. For best results, warm the cleaning solution to about 40 °C [104 °F].

Health and Safety

Please see the 836-P **Safety Data Sheet** (SDS) for more details on transportation, storage, handling and other security guidelines.

Application Instructions

Apply flux by direct dispensing via the pen.

Packaging and Supporting Products

<i>Cat. No.</i>	<i>Form</i>	<i>Net Volume</i>		<i>Net Weight</i>	
836-P 836LFNC-1L	Pen	10 mL	0.33 fl oz	8.0 g	0.25 oz
	Liquid	1 L	33 fl oz	800 g	1.7 lb

Suitable Flux Cleaners

- *Heavy Duty Flux Remover*: Cat. No. 413B-1L, 413B-4L, 413B-20L, 413B-425G
- *Flux Remover for PC Boards*: Cat. No. 4140-P, 4140-400G, 4140-1L, 4140-4L, 4140-20L



ISO 9001 Registered Quality System.
Burlington, Ontario, Canada QMI File # 004008

No Clean Flux Pen 836-P Technical Data Sheet

836-Pen

Technical Support

Contact us regarding any questions, improvement suggestions, or problems with this product. Application notes, instructions, and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Phone: 1-800-340-0772 (Canada, Mexico & USA)

1-905-331-1396 (International)

Fax: 1-905-331-2862 or 1-800-340-0773

Mailing address: **Manufacturing & Support**
1210 Corporate Drive
Burlington, Ontario, Canada
L7L 5R6

Head Office
9347-193rd Street
Surrey, British Columbia, Canada
V4N 4E7

Disclaimer

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. *M.G. Chemicals Ltd.* does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.