

## 4-Port Desktop KVM Switch (USB)

MODEL NUMBER: **B006-VU4-R**



### Description

Tripp Lite's 4-port Desktop USB KVM Switch is the optimal solution for controlling up to 4 USB computers from one VGA monitor and USB keyboard/mouse. Manually switch between connected computers using pushbuttons or hotkey controls; or, monitor connected computers automatically via Auto Scan Mode. The B006-VU4-R is operating system independent, and works with all computers that have an available VGA and USB port. It supports video resolutions up to 2048 x 1536, and features a compact design that does not require software or complicated set-up procedures. Constructed of heavy-duty steel housing. Order P758 Cables separately.

### Features

- Control up to 4 USB computers from a single VGA monitor and USB keyboard/mouse
- Order P758 Cables separately
- Port LEDs illuminate Light Orange to indicate a computer is connected, and Bright Orange to indicate it is the selected port
- Supports video resolutions up to 2048 x 1536, DDC2B
- No software or complicated set-up procedures required
- Manually switch between connected computers via front panel pushbuttons or hotkey commands
- Automatically monitor connected computers via Auto Scan Mode
- Compatible with all major operating systems
- Compatible with most mice; including scroll mice
- Constructed of heavy-duty steel housing

### Highlights

- Control up to 4 USB computers from a single VGA monitor and USB keyboard/mouse
- Switch between connected computers via pushbuttons or hotkey commands
- Auto Scan Mode allows monitoring of connected computers without manually switching between them
- Compatible with all major operating systems
- Supports video resolutions up to 2048 x 1536, DDC2B

### Package Includes

- B006-VU4-R 4-port USB KVM Switch
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A / Output: 5.3V, 190mA)
- Owner's manual

## Specifications

### OVERVIEW



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

UPC Code	037332152947
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A / Output: 5.3V, 190mA
Console	No
Max CPU	4
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	3.50 x 9.80 x 8.70
Shipping Dimensions (hwd / cm)	8.89 x 24.89 x 22.10
Shipping Weight (lbs.)	2.20
Shipping Weight (kg)	1.00
Unit Dimensions (hwd / in.)	1.7 x 7.9 x 2.9
Unit Dimensions (hwd / cm)	4.32 x 20.07 x 7.37
Unit Weight (lbs.)	1.50
Unit Weight (kg)	0.68
LCD Monitor (in.)	N/A
LCD Monitor (cm)	Not Applicable
<b>COMMUNICATIONS</b>	
Port Control	Push Buttons, Hotkeys
IP Remote Access	No
<b>CONNECTIONS</b>	
Ports	4
Computer/Server Ports - Port 1	(x4) HD15 Male
Computer/Server Ports - Port 2	(x4) USB B Female
PC/Server Connections	USB; VGA
<b>FEATURES &amp; SPECIFICATIONS</b>	
Number of Users	1
NIAP-Certified Secure	No
Cat5 KVM Switch	No
Technology	USB; VGA/SVGA
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>