



**HL-6R** - DUAL POWER DUAL LED INDUSTRIAL HEADLIGHT  
NEW

**USB**  
CHARGING

**CREE**  
LEDs



DUAL POWER BATTERY PACK  
RECHARGEABLE & 2 X AA

450

LUMEN  
OUTPUT

4½-96

HOURS  
RUNTIME

129

METRE  
BEAM RANGE

IPX6

WATER  
RESISTANCE

- 450 Lumen White Dual CREE® LEDs
- Spot beam & floodlight functions
- Dual battery - rechargeable & 2 x AA options
- High power 2600mAh Li-ion battery (included)
- Super tough construction
- Micro-USB rechargeable (cable included)
- 3 ½ hours charge time

- 45° rotational head
- Fully adjustable non-slip silicone headbands
- Presented in wet suit zip pouch

**BATTERY** 3.7v 2600mAh Li-ion Rechargeable Battery (inc.) / or 2 x AA Alkaline Batteries (batteries not included)

**WEIGHT** 141g (without batteries)

**DIMENSION** Headlight: 50 x 47 x 38mm - Battery Pack: 42 x 85 x 40mm