



Stellar Labs Part # 24-15082 RED Jacket

20 AWG (Strand) Tinned Copper Wire UL Style 1007 and UL Style 1569 VW-1 80°C / 105°C 300 Volts CSA TR PVC FT1, Hook Up Wire

Product Construction
Conductor:

- 20 AWG Stranded Tinned Copper Wire
- Stranded Tinned Copper Wire Conductor per ASTM B-33

Insulation:

- UL 1007 color coded PVC
- Temperature: -40° to +80°C
- UL 1569 color coded PVC
- Temperature: -40°C to +105°C
- Voltage Rating: 300 volts

Applications:

- Stranded TC wire UL Style 1007 / UL Style 1569 80°C / 105°C 300 Volt Hook-Up Wire
- Point to point wiring
- Internal wiring of meters, panels, electrical and electronic equipment

Industry Approvals:

- UL Style 1007
- UL Style 1569
- CSA-TR-64
- RoHS Compliant
- OSHA acceptable

Packaging:

- 1000 ft. spools
- 100 ft. spools
- Also available on bulk reels



Specifications

Gauge	20 AWG
Strands	Strand Tin Copper Wire
Nominal Insulation Wall	0.015 in
Insulation Type	PVC
Nominal O.D.	0.070 in
Insulation Temperature	UL Style 1007 -40 to +80 °C UL Style 1569 -40 to +105 °C
Voltage Rating	300 V

Other Information

Approvals	CSA TR-64 90°C RoHS Compliant UL 1007, UL 1569 VW-1
-----------	--