

88 KNIPEX Alligator® Water Pump Pliers

DIN ISO 8976








IEC 60900 DIN EN 60900



88 07 250



- More output and comfort compared to conventional water pump pliers of the same length: offer 9 adjustment positioning for 30% more gripping capacity
- Good access to the workpiece due to slim size in the head and joint area
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: low wear and reliable gripping
- Box-joint design: high stability because of double guide
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

Product Number	UPC 8432210-		Pliers	Head	Handles	 Ø Inch	 Ø Inch / Ø mm	 Inch / mm	adjustment positions	 Inch / mm	 lbs
88 07 300	05498		chrome plated		plastic dipped insulated, VDE-tested	2 3/4	2 3/4 70	2 3/64 60	9	12 300	1,457
88 08 250 US	05504			polished	insulated with two-colour dual component handles, VDE-tested	1 31/32	1 31/32 50	1 13/16 46	9	10 250	0,825

technical change and errors excepted

