

DCM340

Digital clampmeter



- DC and AC current and voltage
- 600 A and 600 V
- Resistance and continuity
- 3½ digit, 4000 count display with backlight
- High resolution digital bargraph
- Peak, min/max and data-hold functions

DESCRIPTION

The DCM340 is a highly versatile instrument and ideal for use in the installation, maintenance, monitoring or checking of a.c. or d.c. electrical systems and equipment.

There are four instruments in the DCM series of clampmeters, including the 400 A a.c. current-only DCM310; the DCM320 which includes voltage and resistance measurement; the DCM330 Fork-Multimeter, which is an open fixed jaw design; and this, the DCM340. Capable of measuring a.c. and d.c. current up to 600 A; a.c. and d.c. voltage up to 600 V; resistance up to 400 Ω ; and frequency up to 400 Hz, the DCM340 is the most versatile in the range.

Current measurement combined with the comprehensive and accurate multimeter functions of the DCM340 eliminate the need to carry around both a clampmeter and multimeter – this instrument does it all.

The large clear digits of the numeric display are complemented by the high-resolution digital bar graph, useful for indicating trending and fluctuation of measurement. The backlight assists use in poorly lit areas such as distribution cupboards and corners of switchrooms; and the data-hold feature enables use on difficult access cables where otherwise the display may be impossible to see.

Min/Max hold provides the ability to store the maximum and minimum d.c. or rms values over a period of time. While storage is taking place, either the present, maximum or minimum value can be displayed. Peak hold stores the maximum and minimum peak value of an a.c. signal at a 10 ms sample rate. The auto-off feature automatically places the meter in

power-save mode after 30 minutes from power-on, but this can be disabled if required for min/max measurements.

Using the Relative mode (REL), a stable value can be stored, the instrument zeroed at that point, and then any variation from that value is displayed as a direct measurement relative to it.

The DCM340 is safety rated to IEC 61010-1 Cat III 600 V, and is drop-tested to 1.2 m onto a hard floor. It is supplied with test leads and a carry case, and a full 1-year manufacturer's warranty.

APPLICATIONS

The DCM340 is designed to be used on electrical systems and equipment where there is a need to measure current, volts, resistance and frequency. It is therefore intended for use while installing, maintaining, fault-finding or monitoring those systems.

The min/max and peak-hold enable maximum load currents from equipment to be identified such as start-up currents to motors and heaters.

With the added benefit of d.c. current measurement, it can also be used in applications including domestic power generation from solar panels and wind-turbines; battery monitoring; automotive uses for charging and load circuits; electric vehicle servicing such as fork-lift trucks; lift maintenance; UPS commissioning, servicing and maintenance; electro-plating plants and welding equipment servicing.

SPECIFICATION

Base specifications only. For detailed specification, refer to User Guide

All accuracies specified at 23°C ±5° <80%Rh

AC Current

Range	Accuracy 50 - 60Hz	Accuracy 61 - 400Hz
0-60.0 A	±1.9% ±7 digits	±2.5% ±7 digits
60.0 - 400.0 A	±1.9% ±5 digits	±2.5% ±5 digits
400 - 600 A	±2.5% ±5 digits	±2.9% ±5 digits

DC Current

Range	Accuracy
0 - 60.0A	±1.5% ±10 digits
60.0 - 400.0A	±1.9% ±5 digits
400 - 600 A	±1.9% ±10 digits

Voltage

Range	Accuracy 50 - 500Hz	DC Accuracy
0 - 400.0 V	±1.0% ±5 digits	±0.7% ±2 digits
400 - 600 V	±1.0% ±5 digits	±0.7% ±2 digits

Input impedance: 1 MΩ // < 100 pF

Resistance and Continuity

Range	Accuracy
0 - 400.0 Ω	±1% ±3 digits

Open circuit voltage: 3 V
Continuity Check: beeper sounds @ < 30 Ω

Frequency

Range	Resolution	Accuracy
20 - 400 Hz	1 Hz	±0.1 % ±2 digits

Sensitivity:	3 A
Peak Hold:	±3% ±15 digits
Sample time:	10 ms
MIN/MAX Hold:	add 15 digits to accuracy for a.c. & d.c. A
Positional error:	±1% of reading

Overload protection: 600 V & 600 A rms

AC conversion: Average sensing rms indication calibrated to the rms value of a sine wave input

Auto power-off: 30 minutes after power-on

LCD

Display:	3½ digit large-scale readout
Count:	4000
Sample Rate:	1.5 per second
Overrange:	"OL"

Power Requirement

1 x 9V PP3 MN1604 6LR61 alkaline cell
Battery life: 200 hours (alkaline)

Operating Temperature

0 °C - 30 °C <80% Rh
30 °C - 40 °C <75% Rh
400 °C - 50 °C <45% Rh

Storage Temperature

-20 °C - +60 °C (<81% Rh)
(batteries removed)

Safety

Overvoltage safety category:	IEC 61010-1 600V CAT III
Operating Altitude:	2000 m
Drop-protection:	1.2 m onto a hardwood surface
Jaw size/maximum conductor:	35 mm diameter
Calibration period:	12 month recommended

Dimensions 68 mm (W) x 237 mm (H) x 42 mm (D)

Weight 225 g including batteries

ORDERING INFORMATION

Item (Qty)	Order Code	Item (Qty)	Order Code
DCM340 Digital clampmeter;		User guide	
600 A ac & dc; 600 V a.c. & d.c.; 400 Ω; 400Hz	1000-305	Replacement test leads	
Included accessories		Red/black test leads with croc clips	6220-779
Batteries		Red/black fused test leads (500 mA) with croc clips	6220-789
Pouch			
Test leads			

UK
Archcliffe Road Dover
CT17 9EN England
T +44 (0) 1304 502101
F +44 (0) 1304 207342
E uksales@megger.com

UNITED STATES
4271 Bronze Way
Dallas TX 75237-1088 USA
T 800 723 2861 (USA only)
T +1 214 333 3201
F +1 214 331 7399

OTHER TECHNICAL SALES OFFICES
Valley Forge USA, College Station USA, Sydney
AUSTRALIA, Täby SWEDEN, Ontario CANADA,
Trappes FRANCE, Oberursel GERMANY, Aargau
SWITZERLAND, Dubai UAE, Mumbai INDIA,
Johannesburg SOUTH AFRICA, Chonburi THAILAND,
Malaga SPAIN

Registered to ISO 9001:2008 Cert no. Q 09250
Registered to ISO 14001:2004 Cert no. EMS 61597
DCM340_DS_en_V03
www.megger.com
Megger is a registered trademark