

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192040018](#)
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp 3 Way Splice for 14-16 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-009-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

General

Product Family Splices
 Series [19204](#)
 Comments 3 Way Connector, 3 Way Connector
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Splices](#)
 Product Name 3 Way, Avikrimp
 UPC 800753051676

Physical

Barrel Type Closed
 Color - Resin Natural
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 4.063/g
 Packaging Type Bag
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Temperature Range - Operating -55° to +105°C
 Wire Insulation Diameter 4.32mm max.
 Wire Size AWG 14, 16
 Wire Size mm² 1.30-2.00

Electrical

Voltage - Maximum 600V

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number B-5YC

Reference - Drawing Numbers

Product Specification PS-19902-009-001, PS-19902-011-001,
 PS-19902-013-001
 Sales Drawing SD-19204-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19204 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade HandCrimp Tool [640010100](#)
 Crimp Head for the AT-200 Pneumatic Hand Tool [640050100](#)