

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0845060001](#)  
**Status:** **Active**  
**Overview:** XRC (Extra Rugged Circular) Sealed Plugs and Receptacles  
**Description:** XRC Sealed Receptacle with Socket Insert, Shell Size 24, 31 Circuits, without Collar

**Documents:**

[3D Model](#) [Packaging Specification PK-84501-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-84501-001-001 \(PDF\)](#)

**Agency Certification**

UL E152602

**General**

Product Family Crimp Housings  
 Series [84506](#)  
 Application Power, Wire-to-Wire  
 Comments See Product Specification, See Product Specification  
 Overview XRC (Extra Rugged Circular) Sealed Plugs and Receptacles  
 Product Name XRC  
 UPC 883906514044

**Physical**

Circuits (maximum) 31  
 Color - Resin Black  
 Flammability 94V-0  
 Gender Receptacle  
 Glow-Wire Capable No  
 Keying to Mating Part Yes  
 Lock to Mating Part Yes  
 Net Weight 50.860/g  
 Number of Rows 0  
 Packaging Type Tray  
 Panel Mount Yes  
 Pitch - Mating Interface N/A  
 Pitch - Termination Interface N/A  
 Temperature Range - Operating -40° to +130°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-84501-001-001  
 Product Specification PS-84501-001-001  
 Sales Drawing SD-84506-001-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[84506](#) Series

**Mates With**

[84505](#) XRC Sealed Plug

**Use With**

[84525](#) XRC Sealed Terminal Socket <br>  
[845060012](#) Hex Nut