

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934456121](#)  
**Status:** **Active**  
**Overview:** [ML-XT Sealed Connection System](#)  
**Description:** ML-XT Sealed 12 Circuit Plug Housing, Pre-Assembled with Small Rear Seal and Cover, Keying Option B, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 934430002-K (PDF)</a>
<a href="#">Product Specification 934430010-P (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 934430010-A (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<a href="#">93445</a>
Application	Power, Signal, Wire-to-Wire
Overview	<a href="#">ML-XT Sealed Connection System</a>
Product Literature Order No	987651-0201
Product Name	ML-XT
UPC	889056308267

**Physical**

Circuits (maximum)	12
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	15.700/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C

**Electrical**

Current - Maximum per Contact	13.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	934430010-A
Packaging Specification	934430002-K
Product Specification	934430010-P
Sales Drawing	934430060-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[93445 Series](#)

**Mates With**

ML-XT Sealed 12 Circuit Receptacle Housing [934446121](#)

**Use With**

ML-XT Female (Socket) Terminal [845250009](#) (Nickel), ML-XT Female (Socket) Terminal [845250032](#) (Selective Gold), ML-XT 12 Circuit Plug Wedgelock [93448](#), ML-XT Blind Cavity Plug [934941000](#)