

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349851601](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Hybrid Sealed Female Connector Assembly, Dual Row, 16 Circuits, Keying Option A, without Connector Position Assurance, Black



Series image - Reference only

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification 334760000-PS-CH-000 \(PDF\)](#)
[Product Specification PS-33476-000-001 \(PDF\)](#)
[Application Specification AS-33472-100-001 \(PDF\)](#)
[Packaging Specification PK-30907-895-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Housings
Series	34985
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	No Connector Position Assurance (CPA) See Sales Drawing (PDF) for cavity type & status See Product Specification for maximum current rating by wire AWG, No Connector Position Assurance (CPA) See Sales Drawing (PDF) for cavity type & status See Product Specification for maximum current rating by wire AWG
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056034852
Physical	
Circuits (maximum)	16
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	24.306/g
Number of Rows	2
Packaging Type	Individual Cell
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001
Packaging Specification	PK-30907-895-001
Product Specification	334760000-PS-CH-000, PS-33476-000-001
Sales Drawing	999-S-016-2-Z02-001, SD-34985-8001-001, SD-34985-8002-001

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[34985](#) Series

Mates With
[34986](#) Male Dual Row Hybrid Sealed Connector

Use With
MX150 Female Terminal [33012](#) , [33001](#) ,
Industry Standard Terminal 2.80mm

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION