

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5023511200](#)
Status: **Active**
Overview: [DuraClik Connector System](#)
Description: DuraClik Wire-to-Board Receptacle Housing, Single Row, 12 Circuits, Natural

Documents:

3D Model	Product Specification PS-502351-002-001 (PDF)
Drawing (PDF)	Packaging Specification PK-502351-001-001 (PDF)
Product Specification PS-502351-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	502351
Application	Signal, Wire-to-Board
Comments	Molex part has an inner-locking system versus an outer-locking system. Molex part with tail protection feature., Molex part has an inner-locking system versus an outer-locking system. Molex part with tail protection feature.
Overview	DuraClik Connector System
Product Name	DuraClik
UPC	887191324050

Physical

Circuits (maximum)	12
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Net Weight	450.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact	3.0A
-------------------------------	------


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-502351-001-001
Product Specification	PS-502351-001-001, PS-502351-002-001
Sales Drawing	SD-502351-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[502351](#) Series

Mates With

[560020](#) , [502352](#) 2.00mm Pitch DuraClik
Wire-to-Board Header

Use With

[560085](#) DuraClik Crimp Terminal AWG
22-26, [50212](#) 2.00mm Pitch Crimp Terminal
AWG 24-30, [56161](#) 2.00mm Pitch Crimp
Terminal AWG 22-26