

ABS 3D Filament

For 3D Printers



Features

- High strength
- Good toughness
- Scratch resistance
- The surface can be polished by using acetone and easy to be coloured

Specification

Print temperature : 220°C to 260°C
Hot bed temperature : 110°C
Print speed : 30 to 60mm/s

Part Number Table

Description	Colour	Part Number
ABS Filament, 1.75mm, 1kg/roll	Black	MC002558
	Green	MC002559
	Grey	MC002560
	Red	MC002561
	Blue	MC002562
	White	MC002563
	Light Blue	MC011439
	Natural	MC011440
	Orange	MC011441
	Silver	MC011442
	Peak Green	MC011443
	Yellow	MC011444
	Gold	MC011445
	Purple	MC011446
	Pine Green	MC011447
	Skin	MC011448
Brown	MC011449	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

www.element14.com
www.farnell.com
www.newark.com

