

# ACS480-04-018A-4



ACS480-04-018A-4 Pcont.max:7,5kW, Icont.max:16,2A

## General Information

Global Commercial Alias	ACS480-04-018A-4
Product ID	3AXD50000047792
ABB Type Designation	ACS480-04-018A-4
EAN	6438177459002
Catalog Description	ACS480-04-018A-4 Pcont.max:7,5kW, Icont.max:16,2A

## Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
EAN	6438177459002
Invoice Description	ACS480-04-018A-4 Pcont.max:7,5kW, Icont.max:16,2A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	FIPSEEXPU US Drive Services SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU FIDRIEXPU

## Technical

Frequency (f)	50/60 Hz
Input Voltage ( $U_{in}$ )	380 ... 480 V
Number of Phases	3
Output Current, Normal Use	17 A
Output Power, Light-Overload Use	7.5 kW
Output Power, Normal Use	7.5 kW

## Additional Information

Product Main Type	ACS480-04-018A-4
-------------------	------------------

Product Name

Frequency Converter

Categories

Drives → Low voltage AC drives → General purpose drives

