

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192030083

Status:

Active

Overview:

High-Temperature Temp Terms Terminals and Splices

Description:

Krimptite Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 8 (M4)

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19203

Comments

1200° F (649° C), 1200° F (649° C)

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

High-Temperature Temp Terms Terminals and Splices

Product Name

Krimptite, Temp-Terms

Type

Ring

UPC

800755059397

Physical

Barrel Type

Closed

Insulation

None

Material - Plating Mating

Tin

Net Weight

0.628/g

Packaging Type

Bag

Stud Size

8 (M4)

Wire Size AWG

14, 16

Wire Size mm²

1.00-2.50

Material Info

Engineering Number

BB-U-137-08

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

BBCD10104



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19203 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand	640030100
Crimp Tool	
Crimp Head for the	640070100
AT-200 Pneumatic	
Hand Tool	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION