

Description

The CiT Builder RGB has everything you would want from a gaming keyboard and will fit right in with your other peripherals. You can switch between 7 different colours at the touch of a button with bright LEDs running throughout to provide true colour lighting.

With a low profile base and minimal boarder, the Builder RGB has a clean and simplistic design. Keeping your set up clutter free.

The Builder has 12 multimedia functions in total ranging from media controls right the way through to office applications, all located on the F key functions. Made from high quality ABS and fitted with a touch membrane under each key, you can expect nothing but a smooth experience when using the keyboard for either gaming or work.

The Builder is designed for gaming, creative or general office work and is a great option if you are looking for fantastic performance and nice aesthetics without paying a small fortune for a keyboard.

Key Features

- **RGB LED Backlight** - There are seven permanent lighting modes to choose from, you can easily change the LED backlight colour, press FN & LED button to cycle through the colours fading in and out and easily adjustable brightness can create an incredibly looking gaming set up and atmosphere.
- **Made Using High Quality Materials** - The Builder is made using high quality touch membrane, creating robust long-lasting keys, allows for excellent durability during use.
- **Gaming Functions** - Press FN and "W" button to change the "W", "S", "A" and "D" with "Up", "Down", "Left" and "Right". To quickly swap the cursor keys for game play.
- **Multimedia Functions** - 12 multimedia functions are on offer with the Builder, press FN & F1-F12 to access these frequently used programs at the touch of a button.
- **USB Connector** - Plug and play, easy to install.

Specifications

Coonectivity: USB

Keyboard Qty: 105

Cable Length: 1.5m

LED Colour: 7 (Red, Green, Blue, Cyan, White, Purple & Yellow)

Working Power: 5V=100mA

M.T.B.F: 5 Million Keystrokes

Multimedia Functions: FN + F1-F12

F1: Open Default Media Player Program

F2: Decrease System Volume

F3: Increase System Volume

F4: Mute System Volume

F5: Stop Current Media Track

F6: Play Previous Media Track

F7: Play Or Pause Current Media Track

F8: Play Next Media Track

F9: Open Default E-mail Program (Not Web-Mail)

F10: Open Home Page

F11: Lock Keys

F12: Open Calculator

Key Elasticity: 44 ± 10g

Key Force: 30 ± 5g

Pre-Travel

Distance of 1.2+/-0.3mm

Keys:

Total Travel

Distance of 6.0 ± 0.3mm

Keys:

Working

Environment -6°C to + 46°C

Temperature:

Operating 10°C to 80°C

Humidity:

Working Voltage: +5V ± 0.25V

Working Current: 100mA (Max)

Software Compatibility: Windows 2000 / XP / ME / Vista / 7 / 8 / 10 / Mac OSX / Linux / Android

Net Weight: 610g

General Specifications

Manufacturer: KB-BUILDERRGB

Part Number:

EAN Number: 5055492407900

Has Mains Plug: Yes

Colour: Black

What's In The Box: Keyboard

Box: Manual

Unit (Product)

Dimensions (mm): 436mm x 30mm x 134mm (W x H x D)

Packaging

Dimensions (mm): 454mm x 160mm x 36mm (W x H x D)

Net Weight (KGs): 0.61 KGs

Gross Weight (KGs): 0.74 KGs