



## **150 ASTM**

## **Splicing Compound Rubber Tape**

Technical Data Sheet October 2017

## Description and Features

**150 ASTM Tape** is a 30 mil (0,76 mm) self-amalgamating, low voltage rubber tape that can be used in conjunction with a jacketing tape, for insulating cable splices through 2 kV. Compatible with low and high-density polyethylene and polypropylene cables plus all rubber and PVC cable elements. **150 ASTM Tape** conforms easily and self-amalgamates into a homogeneous, void-free mass to provide an effective moisture seal. ASTM D4388, Communications Industry Specification 6746.

- Self- amalgamating
- · Good electrical properties
- Effective moisture seal
- Good conformability

Materials	<b>Backing</b> Rubber	Adhesive none	<b>Color</b> Grey	Standard Size Width x Length 19 mm x 9,1 m (0.75 in. x 30 ft.) Other sizes available upon request	
Technical Properties	Characteris	stic		Typical Value	Test Method
	Thickness (mm)			0,76	ASTM D 4325
	Tensile strength (MPa)			2,0	ASTM D 412
	Elongation (%)			500	ASTM D 412
	Fusion (2,0 mm max.)			No flag	ASTM D 4325
	Heat resistance (°C)			95	ASTM D 4325
	Operating temperature (°C)				
	Continuous			80	<b>ASTM D 4325</b>
	Emergency overload			95	ASTM D 4325
	Dielectric strength (kV/mm)			20	ASTM D 149
Recommended Uses	For insulating of splices on solid dielectric cable thru 2 kV in conjunction with a jacketing tape.				
Storage	In original packaging, placed in horizontal position under cover and temperature between 5°C and 35 °C.				
Shelf Life	24 months from date of manufacture.				

Information provided is for reference only. Data in table represent average test results and are not to be used for specification purposes. The product user should make his/her own tests to determine the product's suitability for the intended use

LIMITED WARRANTY: Plymouth warrants that its Product will substantially conform to that products written specifications for a period of one (1) year from the date of shipment, (Unless provided otherwise). Plymouth makes no warranty to the distributor, its customers, or the product's end user for the products merchantability and/or suitability for his/its intended use or purpose, and buyer shall have first compiled with all return policies of Plymouth, PLYMOUTH'S SOLE OBLIGATION AND BUYER'S EXCLUSIVE REMEDY UNDER THIS PRODUCT WARRANTY SHALL BE TO REPLACE SUCH QUANTITY OF THE PRODUCT AS IS PROVED TO BE DEFECTIVE WITHIN THE TIME PERIOD SPECIFIED ABOVE. EXCEPT AS EXPRESSLY SET FORTH HEREIN, PLYMOUTH MAKES NO OTHER ARRANTIES, EXPRESS OR IMPLIED. In no event shall Plymouth be liable for collateral, consequential, indirect or incidental damages arising out of, or connected in any way with the supply of products. (Rev. 1/2017-2019)