


DVI-D Plug to DVI-D Plug Dual Link Digital Video Cable Assembly 5m (16.4 Ft)



Specifications


Connector Type A	: DVI-D Plug
Connector Type B	: DVI-D Plug
Cable Length	: 5m (16.4 Ft)
Jacket Colour	: Black
Contact Resistance	: 6Ω Max.
Insulation Resistance	: 10MΩ Min.
Hi-Pot	: 100V DC/10ms

Diagram



Dimensions : Millimetres

PIN Assignment



No	Description	Qty	Unit
1	UL20276~[28AWG(7/0.127TC)+EAM]×7P+28AWG(7/0.127TC)×1P+28AWG(7/0.127TC)×3C+AEB(16/5/0.12AL50% AL)~OD: 8.5mm~Colour: Black	L	m
2	DVI (24+1)M Insulation Black shell Gold Plated	2	Pcs
3	Tinplate: OD: 9.5mm	2	Pcs
4	45P PVC Colour: Black	60	g
5	#4-40UNC 2.8×4.5mm Nickel plated	4	Pcs
6	DVI M Transparent dust cover	2	Pcs
7	DVI (24+1)M Black wire clip to double row 28AWG	2	Pcs
8	Copper foil: 25μ ~ W = 8mm	0.08	M
9	Core: 28.5×17.5×9.5mm	2	Pcs
10	30P PVC Colour: Black	10	g

Part Number Table

Description	Part Number
DVI-D Plug to DVI-D Plug Dual Link Digital Video Cable Assembly 5m (16.4 Ft)	10DV-07105-G