









8	A02400000003	Heat sinks`24*15*1.5mm	1	pcs	REV	DESCRIPTION			DATE		
7	A5-R047165	TPE`45P`Black	10	g		TOLERANCE INCHES M/M		TITLE:			
6	A10-R042106	Double conductive copper foil`25u`W=5MM	0.025	m		.X	.015				.30
5	A0021700-00071	Brass buckle:11x7x6mm`OD:4.5mm`Surface of the tin plating	1	pcs		.XX	.010				.10
4	A0020200-10529	2.5GE ABS block head (M01-00537)`Black`No mark	1	pcs	.XXX	.005	.05	CUSTOMER : CPC			
3	A0020200-10528	2.5GE ABS shell (M01-00536) `Black`Mark:2.5G	1	pcs	DRAWN BY						CUSTOMER P/N : CS32425
2	B010-02432	UTC-2.5GE(PCB+SMT)	1	pcs	CHECK BY			SCALE	NONE		REV. A1
1	B000-07563	USB3.0 AM TO AM`30+28AWG`OD:4.2MM`BLACK ABS`L=0.4M	1/2	pcs				UNIT	MM		1/2
NO		DESCRIPTION	Q' TY	UNIT	APPD BY			DATE	2019.04.08		



REV	DESCRIPTION				DATE
	TOLERANCE		TITLE:		
	INCHES	M/M			
	.X	.015 .30			
	.XX	.010 .10			
	.XXX	.005 .05			
DRAWN BY			CUSTOMER :	CPC	
CHECK BY			CUSTOMER P/N :	CS32425	
APPD BY			SCALE	NONE	REV. A1
			UNIT	MM	
			DATE	2019. 04. 08	2/2

NO	DESCRIPTION				Q' TY	UNIT
----	-------------	--	--	--	-------	------