


miniMEDIA Category 6 1U 12 port patch panel



miniMEDIA Category 6 1U 12 port patch panel (SF12ep)

Our new Category 6 12 port patch panel is equipped with dual Krone-style/110 IDC connectors and perfectly compliments the other items in our *miniMEDIA* 10" SOHO range

Features

- Category 6 EIA/TIA 568B permanent link standard
- Complements other items in our **miniMEDIA** 10" range for SOHO installations
- Robust and high quality metal construction
- LSA/110 style IDC connections, colour coded to both T568a and T568b wiring
- Supplied with cage nut set and cable ties

Specifications

Weight: 288g

Dimensions: 255 x 44 x 30mm

Colour: black



Material:

Front plate: Fireproof ABS UL-94V0 Panel: cold rolled steel (SPCC)

Socket contacts: 8p8c 50µ"/1.27µm gold plated

PCB: FR-4 / UL-94V0

• IDC description:

Suitable for 22-26 AWG/ 0.65-0.40mm Designed for termination with 110 or LSA+ type punch-down tool

Electrical specifications:

• Insulation resistance: 500MΩ (min.)

Contact resistance: 20mΩ (max.)

• Current rating: 1.5 Amps

• DC resistance: 0.1Ω (max.)

• Withstand voltage: 1000 VAC RMS @ 60Hz/1min.

Mechanical specifications:

• IDC punch down cycle: over 250 cycles (min.)

• Jack insertion cycle: over 2000 cycles (min.)

Operation temperature: -40°C ~ +70°C

Packaging: Supplied in a labelled white carton

EAN: 5055386507365

Commodity Code: 851777090